

型号说明 Ordering Information

IRS-101-1A3D-R/B

- 基座颜色 Base color
- 盖帽颜色 Cap color
- 直流灯 DC lamp
- 盖帽标记 Cap marking
- 盖帽种类 Cap options
- 产品序号 Product order
- 电路特性 Circuitry trait
- 刀数 Poles
- IRS带灯波动开关 Illuminated Rocker Switch
- RS不带灯波动开关 Rocker Switch

技术特性 Specification

- 1.规格 Rating:20A 125VAC;15A 250VAC;35A 12VDC
- 2.接触电阻 Contact Resistance:35mΩ max
- 3.绝缘电阻 Insulation Resistance:500VDC 100MΩ min
- 4.耐电压 Dielectric Strength:1500VAC, 1Minute
- 5.操作温度 Operating Temperature:-25°C ~ +85°C
- 6.电气寿命 Electrical Life:10,000 Cycles

电路特性Circuitry trait


01	ON	-	OFF
02	ON	-	ON
11	(ON)	-	OFF
03	ON	OFF	ON
13	ON	OFF	(ON)
23	(ON)	OFF	(ON)

() : 回弹指示 Indicates Momentary


盖帽颜色Cap color 基座颜色Base color 盖帽种类Cap options

黑 Black (B)
 白 White (W)
 红 Red (R)
 黄 Yellow (Y)
 绿 Green (G)
 蓝 Blue (BL)
 桔黄 Orange (O)
 灰 Gray (GR)

黑 Black (B)
 白 White (W)
 灰 Gray (GR)



盖帽标记 Cap marking



防水罩 Water proof cap

