
### **Spec Sheet**

# Multilayer Chip Bead Inductors (BK series)

## BK0603HS330-T



#### Features

- Item Summary  $33\,\Omega,\,0.5\,\text{A},\,0201/0603\,\text{(EIA/JIS)}$
- Lifecycle Stage

Mass Production

Standard packaging quantity (minimum)
Taping paper 15000pcs

#### Products characteristics table

Impedance [100MHz]	33 Ω ± 25 %
Case Size (EIA/JIS)	0201/0603
Rated Current (max)	0.5 A
DC Resistance (max)	70 mΩ
Z Measuring Frequency	100 MHz
Operating Temp. Range	-55 to +125 ℃
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow

#### ■ External Dimensions

Dimension L	0.6 ±0.03 mm
Dimension W	0.3 ±0.03 mm
Dimension T	0.3 ±0.03 mm
Dimension e	0.15 ±0.05 mm

The data is reference only. Electrical characteristics vary depending on environment or measurement condition. TAIYO YUDEN reserves the right to make change to the Date at any time without notice. Before making final selection, please check product specification.