





Replacement Nozzle:

IC Package	IC (mm)	Model No.	AxB (mm)	CxD (mm)
Single 		9SS-900-A1	Ø2.2 (I.D)	
		9SS-900-A2	Ø6.6 (I.D)	
		9SS-900-A3	Ø8.5 (I.D)	
QFP (Quad Flat Pack) 	10x10	9SS-900-B	10.2x10.2	10x10
	14x14	9SS-900-C	15.2x15.2	15x15
	17.5x17.5	9SS-900-D	19.2x19.2	19x19
	14x20	9SS-900-E	15.2x21.2	15x21
	28x28	9SS-900-F	29.7x29.7	29x29
SOP (Small Outline Package) 	4.4x10	9SS-900-H	10x4.8	
	5.6x13	9SS-900-I	15x5.7	
	7.5x15	9SS-900-J	16x7.2	
	7.5x18	9SS-900-K	19x7.2	
PLCC (Plastic Leaded Chip Carrier) 	17.5x17.5	9SS-900-L	18.5x18.5	15x15
	20x20	9SS-900-M	21x21	19x19
	25x25	9SS-900-N	26x26	24x24
	30x30	9SS-900-O	31x31	29x29

Model No.	Voltage	Consumption	Temperature	Nozzle	Replacement heater	Standard Plug
SS-601A	100~120V	5~500W	100°C~ 480°C (212°F~ 896°F)	9SS-900-A1(Ø 2.2mm)x 1pcs 9SS-900-A2(Ø 6.6mm)x 1pcs	9SS-601A-H	A
SS-601F	220~240V	5~600W	100°C~ 480°C (212°F~ 896°F)	9SS-900-A3(Ø 8.5mm)x 1pcs	9SS-601B-H	F