


pin number	pin name
G1	switch
pin 8	RSV
pin 7	DO
pin 6	VSS
pin 5	SCLK
pin 4	VDD
pin 3	DI
pin 2	CS
pin 1	RSV

STEP III PUSH SHELL (C1/C2 SWITCH LOCK)

- NOTES:
1. MATERIAL:
 - 1.1 Housing: High Temperature Thermoplastic UL94V-0, Color Black.
 - 1.2 Terminal: Copper Alloy.
 - 1.3 Shell: Stainless Steel.
 2. SPECIALTY:
 - 2.1 Rated current: 0.5A
 - 2.2 Rated voltage: 30V
 - 2.3 Contact Resistance: 50mΩ MAX
 - 2.4 Insulation Resistance: 100MΩ MIN 100V
 - 2.5 Dielectric withstanding voltage: 100V AC.
 - 2.6 Solder ability: 235±5°C, 5±0.5s.
 - 2.7 Durability: 5000 Cycles Min.
 - 2.8 Operating condition: Temperature -40°C~+85°C;

Humidity 80% R.H MAX
 3. PLEASE CONTACT JITS SALES REPRESENTATIVE TO VERIFY PRODUCT DETAILS & AVAILABILITY



RECOMMEND PCB LAYOUT
 RECOMMEND TOLERANCE: +/-0.05MM
 FRAME DF CONNECTOR: - - - - -

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
③	Shell	---	1	SUS	Ni Plated	---
②	Terminal	---	9	Phosphor Bronze	Sn Plated	---
①	Housing	---	1	Thermoplastic	Black	---

APPROVALS	DATE	TITLE:
DRAWN JKUN/LU	2018/8/1	ELECTRONICS CO.,LTD
CHECKED		TF

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

TOLERANCES ARE	ANGLE	UNIT:	SCALE:	PROJ:	SHEET
30~Ø以上 ±0.30 10~30 ±0.25 5~10 ±0.20 ~5 ±0.15	±2'	mm	1:1	TF-06A	1 OF 1