

Product number: 037161



Description:

Brand: Legrand
 Series: Viking3 klemmenstroken
 Product Class: Verbindingsrijgklem
 Price (per 1 st):
 Start Date: 1-1-2014
 Discount Group: L5
 Net Weight (kg): 0,009

Features

Connectable conductor cross section fine-strand without cable (mm ²):	0.25 - 4	Connectable conductor cross section solid-core (mm ²):	0.25 - 6
Connectable conductor cross section multi-wired (mm ²):	0.5 - 1.5	Rated current I _n (A):	32
Rated voltage (V):	500	Type of electrical connection 1:	Screw connection
Type of electrical connection 2:	Screw connection	Connection position:	Sideways
Number of levels:	1	Number of clamp positions per level:	2
Mounting method:	DIN rail (top hat rail) 35 mm	Material insulation body:	Other
Operation temperature (°C):	-5 - 40	Inflammability class of insulation material acc. with UL94:	V2
Width/grid dimension (mm):	52.2	Height at lowest possible mounting height (mm):	46.4
Explosion-tested version 'Ex e':	Yes	Closing plate required:	Yes
Colour:	Grey	Internally connected stages:	No
Height (mm):	46.4	Material:	Plastic
Surface treatment:	Polyamide		

Prices are valid for the Dutch market. All prices are gross, excluding VAT. Technical and / or price changes and mistakes are possible.