

34136 -- 1 of 1 products

Terminals and Splices Splices - Closed Barrel





Line art represents typical product only.

Searchable Features:	
Product Type	Splice
Splice Type	Parallel
Body Style	PLASTI-GRIP
Insulation	Yes
Insulation Support	Insulation Support
Insulation Diameter	.230 [5.84] Max. in. [mm]
Wire Range	12-10 [2.62-6.64 ²] AWG [mm]
Wire Range (CMA)	5,180-13,100
Material	Copper
Finish	Tin
Packaging Method	Loose Piece
Other Properties:	
Dim. L	.870 [22.10] Max. in. [mm]
Color	Yellow
CERTI-CRIMP Hand Tool 59270-0, 675999-0	