

F10-IP65 Series is a range of Low Power IP65 Rated LED Flexible Strips suitable for domestic, commercial and retail internal lighting applications.

- Energy Saving
- Compact strip with SMD LED Technology
- Non yellowing, scratch resistant UV stable resin
- Water Resistant to IP65 level*
- 50k hours working life
- High Reliability & Efficiency
- 60 LEDs per metre
- Cuttable every 50mm
- 120° beam angle

Applications


- Accent Lighting
- Cabinet Lighting
- Mood Lighting
- Cove Lighting
- Under Cabinet Lighting
- Bookshelf Lighting
- Display Cabinet Lighting



Low Power IP65 Rated Energy Saving LED Flexi Strips

★ Flexi Strip Specification


Power	4.8W per metre
Input	12V
LEDs Per Meter	60
Cuttable Length	every 50mm
IP Rating	IP65
Length	5 Metres



IP65



Part number	Wave Length	Lumens/mtr	Colour
F10-R3528-12-60-IP65	620nm	90LM	Red
F10-G3528-12-60-IP65	520nm	180LM	Green
F10-B3528-12-60-IP65	470nm	60LM	Blue
F10-W3528-12-60-IP65	-	320LM	3000K (warm white)
F10-C3528-12-60-IP65	-	380LM	6000K (cool white)



*Product not fully IP65 Rated unless IP65 Rated connections & power supply used
Representative colours may change; purchase from the same batch code for colour consistency

We recommend a maximum of 15mtrs strip per driver due to possible voltage drop