

Malleable cast iron fittings

245

Hexagon nipple, reducing, ISO/EN N8

ST ... these types of fittings are made from steel (galvanised finish = electroplated) and not suitable for drinking water installations.



	Dim. (1-2) [inch]	EN	Code	SP	kg	a [mm]	s [mm]
ST B	1/4 - 1/8	-	770 245 115	10	0.026	35	17
ST G	1/4 - 1/8	-	770 245 215	10	0.026	35	17
ST B	3/8 - 1/8	-	770 245 116	10	0.032	34	19
ST G	3/8 - 1/8	-	770 245 216	10	0.032	34	19
ST B	3/8 - 1/4	•	770 245 117	10	0.035	38	19
ST G	3/8 - 1/4	•	770 245 217	10	0.035	38	19
B	1/2 - 1/4	•	770 245 118	10	0.063	44	27
G	1/2 - 1/4	•	770 245 218	10	0.066	44	27
B	1/2 - 3/8	•	770 245 119	10	0.054	44	22
G	1/2 - 3/8	•	770 245 219	10	0.056	44	22
B	3/4 - 1/4	-	770 245 120	10	0.087	43	30
G	3/4 - 1/4	-	770 245 220	10	0.091	43	30
B	3/4 - 3/8	•	770 245 121	10	0.085	47	30
G	3/4 - 3/8	•	770 245 221	10	0.090	47	30
B	3/4 - 1/2	•	770 245 122	10	0.095	47	31
G	3/4 - 1/2	•	770 245 222	10	0.099	47	31
B	1 - 1/2	•	770 245 123	10	0.151	53	36
G	1 - 1/2	•	770 245 223	10	0.156	53	36
B	1 - 3/4	•	770 245 124	10	0.159	53	36
G	1 - 3/4	•	770 245 224	10	0.166	53	36
B	1 1/4 - 1/2	•	770 245 125	25	0.179	57	46
G	1 1/4 - 1/2	•	770 245 225	25	0.184	57	46
B	1 1/4 - 3/4	•	770 245 126	60	0.193	57	46
G	1 1/4 - 3/4	•	770 245 226	60	0.199	57	46
B	1 1/4 - 1	•	770 245 127	50	0.245	57	46
G	1 1/4 - 1	•	770 245 227	50	0.253	57	46
B	1 1/2 - 3/4	•	770 245 128	20	0.292	59	50
G	1 1/2 - 3/4	•	770 245 228	20	0.301	59	50
B	1 1/2 - 1	•	770 245 129	50	0.280	59	50
G	1 1/2 - 1	•	770 245 229	50	0.287	59	50
B	1 1/2 - 1 1/4	•	770 245 130	40	0.289	59	50
G	1 1/2 - 1 1/4	•	770 245 230	40	0.301	59	50
B	2 - 1	•	770 245 131	25	0.508	68	65
G	2 - 1	•	770 245 231	25	0.519	68	65
B	2 - 1 1/4	•	770 245 132	25	0.396	68	65
G	2 - 1 1/4	•	770 245 232	25	0.418	68	65
B	2 - 1 1/2	•	770 245 133	20	0.552	68	65
G	2 - 1 1/2	•	770 245 233	20	0.550	68	65
B	2 1/2 - 1 1/2	-	770 245 134	15	0.573	75	80
G	2 1/2 - 1 1/2	-	770 245 234	15	0.589	75	80
B	2 1/2 - 2	•	770 245 135	10	0.690	75	80
G	2 1/2 - 2	•	770 245 235	10	0.722	75	80
B	3 - 2	•	770 245 136	8	1.070	83	95
G	3 - 2	•	770 245 236	8	1.096	83	95
B	3 - 2 1/2	•	770 245 137	8	1.047	83	95
G	3 - 2 1/2	•	770 245 237	8	1.050	83	95
B	4 - 3	-	770 245 138	12	1.360	93	120
G	4 - 3	-	770 245 238	12	1.405	93	120

The technical data are not binding and not expressly warranted characteristics of the goods. They are subject to change. Our General Conditions of Sale apply.

Georg Fischer Piping Systems Ltd, Postfach, CH-8201 Schaffhausen/Switzerland
Phone +41 -(0)52-631 1111
e-mail: info.ps@georgfischer.com
Internet: <http://www.piping.georgfischer.com>