


RGBW LED Flexi Strip



- Even LED RGB colour and white lighting
- High quality UV stable polyurethane sleeving enables non discolouration and is scratch resistant for longer life
- Optional high grade thick VHB 3M adhesive backing tape can be supplied
- Available in IP20, IP65 & IP67 ratings
- 50,000 hours working life
- Multiple applications for commercial and residential environments
- Precise LED binning enables 100% consistent colour temperature from batch to batch

30
LEDs/m

60
LEDs/m



Specification

Part Code	F10-RGBW-12-30-FP
Voltage	12VDC
Power Consumption	9.6W per mtr
LED Qty	30 per mtr
PCB Width	10mm
White & RGB Colour mixing	Parallel in line
IP	IP20/65/67 available
IP67 Finish	Glue filled silicon tube
Working Temperature	-30°C ~ +70°C
Dimensions	5000mm

Mechanical Diagrams

