


ISO 4029

DIN 916

45 H

**BN 27****Hex socket set screws**

with cup point

Steel 45 H

black

- ~UNI 5929

Set screws are *not* intended to be tensile-loaded.

M14: not included in ISO 4029

Article#	d ₁	d ₂	s	t min.	L
1031732	M1,6	0,55-0,8	0,7	1,5	2,5
1031740					3
1031759					4
1031848	M2	0,75-1	0,9	0,8	2,5
1031856				1,7	3
1031864					4
1031872					5
1031880					6
1031899					8
1031902					10
1031988	M2,5	0,95-1,2	1,3	1,2	3
1031996				2	4
1032003					5
1032011					6
1032038					8
1032046					10
1032119	M3	1,15-1,4	1,5	1,2	3
1032127					4
1032135				2	5
1032143					6
1032151					8
1032178					10
1032186					12
1032194					(14)
1032216					16
1032232					20

M14: not included in ISO 4029

Article#	d ₁	d ₂	s	t min.	L
1032259	M3	1,15-1,4	1,5	2	25
3055875					30
1919547	M4	1,75-2	2	1,5	3
1032267					4
1032275					5
1032283				2,5	6
1032291					8
1032305					10
1032313					12
1032321					(14)
1032356					16
1032364					(18)
1032372					20
1032399					25
1032402					30
1032410					35
1032429					40
1032461	M5	2,25-2,5	2,5	2	5
1032488				3	6
1032496					8
1032518					10
1032526					12
1032534					(14)
1032550					16
1032577					20
1032585					(22)
1032593					25
1032607					30
1032615					35
1032623					40
1032674	M6	2,75-3	3	2	5
1032682					6
1032690				3,5	8
1032704					10
1032712					12
1032720					(14)
1032747					16
1032755					(18)
1032763					20
1032771					(22)
1032798					25

M14: not included in ISO 4029

Article#	d ₁	d ₂	s	t min.	L
1032801	M6	2,75-3	3	3,5	30
1032828					35
1032836					40
3055876					50
1032879	M8	4,7-5	4	3	6
1032887					8
1032895				5	10
1032909					12
1032917					(14)
1032933					16
1032941					(18)
1032968					20
1032976					(22)
1032984					25
1032992					30
1033034					35
1033042					40
1033069					50
1033077					60
3055878					70
1920693	M10	5,7-6	5	4	8
1033107					10
1033115				6	12
1033123					(14)
1033158					16
1033174					20
1033190					25
1033204					30
1033212					35
1033220					40
1033247					50
1033255					60
1033301	M12	7,64-8	6	4,8	12
1033328				8	(14)
1033344					16
1033360					20
1033387					25
1033395					30
1033409					35
1033417					40
1033425					45

M14: not included in ISO 4029

Article#	d ₁	d ₂	s	t min.	L
1033433	M12	7,64-8	6	8	50
1033441					60
1033476					80
1033492	(M14)	8,64-9	6	5,6	(14)
1033514				9	16
1033530					20
1033557					25
1033565					30
1033581					40
1033611					50
1033697	M16	9,64-10	8	6,4	16
1033719				10	20
1033735					25
1033743					30
1033751					35
1033778					40
1033794					50
1033808					60
1033816					70
1033824					80
1033972	M20	13,57-14	10	8	20
1033999				12	25
1034006					30
1034014					35
1034022					40
1034049					50
1034057					60