



MATERIALS:

Body and Fittings: Brass, Tarnish Resistant Plating

Center Contact: Gold Plated Beryllium Copper

Dielectric: PTFE

Finish: Body and Fittings: Tarnish Resistant

Center Contact: Gold Plated

RATING:

Nominal Impedance: 50 Ohms

Operating Temperature: -65°C to $+165^{\circ}\text{C}$

ORDERING INFORMATION: Model 2451

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA