


Model Type: EC-4010xxxx
 Dimension : 40 x 40 x 10 mm

	Voltage	5V		12V		24V	
		✓		✓			
	Fan Speed	LL	L	M	H	HH	TH
		4000	4500	5000	5500	6000	6500
	Certificate	UL		CE		TUV	
		✓		✓		✓	
	Bearing Type	Sleeve		1 Ball	2 Ball	EL	
		✓		✓	✓	✓	

Model	Voltage VDC	Current AMP	Input Watts	Fan Speed RPM	AirFlow (Max) CFM	Pressure InchH ₂ O	Noise dBA	Life Hour
EC4010HH05B	5	0.18	0.9	6000	6.24	0.15	<25	50000
EC4010HH05C								35000
EC4010HH05S								25000
EC4010HH05E								40000
EC4010H05B	5	0.14	0.7	5500	5.75	0.13	<23	50000
EC4010H05C								35000
EC4010H05S								25000
EC4010H05E								40000
EC4010M05B	5	0.12	0.60	5000	5.22	0.1	<21	50000
EC4010M05C								35000
EC4010M05S								25000
EC4010M05E								40000
EC4010L05B	5	0.1	0.5	4500	2.71	0.09	<19	50000
EC4010L05C								35000
EC4010L05S								25000
EC4010L05E								40000
EC4010LL05C	5	0.08	0.4	4000	2.5	0.08	<17	50000
EC4010LL05B								35000
EC4010LL05S								25000
EC4010LL05E								40000
EC4010TH12B	12	0.12	1.44	6500	6.64	0.16	<26	50000
EC4010TH12C								35000
EC4010TH12S								25000
EC4010TH12SE								25000
EC4010HH12B	12	0.1	1.2	6000	6.24	0.15	<25	50000
EC4010HH12C								35000
EC4010HH12S								25000
EC4010HH12E								40000
EC4010H12B	12	0.18	0.96	5500	5.75	0.13	<23	50000
EC4010H12C								35000
EC4010H12S								25000
EC4010H12SE								40000
EC4010M12B								50000

EC4010M12C	12	0.07	0.84	5000	5.22	0.1	<21	35000
EC4010M12S								25000
EC4010M12E								40000
EC4010L12B	12	0.05	0.6	4500	2.71	0.09	<19	50000
EC4010L12C								35000
EC4010L12S								25000
EC4010L12E								40000
EC4010LL12B	12	0.04	0.48	4000	2.5	0.08	<17	50000
EC4010LL12C								35000
EC4010LL12S								25000
EC4010LL12E								40000

E--EL bearing, B -- Two ball bearing, C -- One ball One sleeve bearing, S -- Sleeve bearing