


**Model Type: EC-6010xxxx**  
**Dimension : 60 x 60 x 10 mm**

	Voltage	5V		12V		24V	
				✓		✓	
	Fan Speed	LL	L	M	H	HH	TH
		3200	3600	4000	4400	4800	5200
	Certificate	UL		CE		TUV	
		✓		✓		✓	
Bearing Type	Sleeve		1 Ball	2 Ball	EL		
	✓		✓	✓	✓		

Model	Voltage VDC	Current AMP	Input Watts	Fan Speed RPM	AirFlow (Max) CFM	Pressure InchH <sub>2</sub> O	Noise dBA	Life Hour
EC6010HH12B	12	0.22	2.64	4800	20.18	0.15	<36	50000
EC6010HH12C								35000
EC6010HH12S								25000
EC6010HH12E								40000
EC6010H12B	12	0.2	2.4	4400	17.7	0.12	<33	50000
EC6010H12C								35000
EC6010H12S								25000
EC6010H12E								40000
EC6010M12B	12	0.16	1.92	4000	15.49	0.1	<30	50000
EC6010M12C								35000
EC6010M12S								25000
EC6010M12E								40000
EC6010L12B	12	0.14	1.68	3600	15.03	1.78	<26	50000
EC6010L12C								35000
EC6010L12S								25000
EC6010L12E								40000
EC6010HH24B	24	0.18	4.32	4800	20.18	0.15	<36	50000
EC6010HH24C								35000
EC6010HH24S								25000
EC6010HH24E								40000
EC6010H24B	24	0.16	3.84	4400	17.7	0.12	<33	50000
EC6010H24C								35000
EC6010H24S								25000
EC6010H24E								40000
EC6010M24B	24	0.14	3.36	4000	15.49	0.1	<30	50000
EC6010M24C								35000
EC6010M24S								25000
EC6010M24E								40000
EC6010L24B	24	0.12	2.88	3600	15.03	0.09	<26	50000
EC6010L24C								35000
EC6010L24S								25000
EC6010L24E								40000
EC6010LL24B								50000

EC6010LL24C	24	0.1	2.4	3200	12.96	0.07	<25	35000
EC6010LL24S								25000
EC6010LL24E								40000

**E--EL bearing, B -- Two ball bearing , C -- One ball One sleeve bearing, S -- Sleeve bearing**