


Model Type: EC-6015xxxx

Dimension : 60 x 60 x 15 mm

	Voltage	5V		12V		24V	
				✓		✓	
	Fan Speed	LL	L	M	H	HH	TH
		3000	3500	4000	4500	5000	5500
	Certificate	UL		CE		TUV	
		✓		✓		✓	
Bearing Type	Sleeve		1 Ball	2 Ball	EL		
	✓		✓	✓	✓		

Model	Voltage VDC	Current AMP	Input Watts	Fan Speed RPM	AirFlow CFM	Pressure InchH <sub>2</sub> O	Noise dBA	Life Hour
EC6015TH12B	12	0.21	2.52	5500	20.73	0.2	<39	50000
EC6015TH12C								35000
EC6015TH12S								25000
EC6015TH12E								40000
EC6015HH12B	12	0.15	1.8	5000	19.42	0.18	<37	50000
EC6015HH12C								35000
EC6015HH12S								25000
EC6015HH12E								40000
EC6015H12B	12	0.11	1.32	4500	18.12	0.16	<32	50000
EC6015H12C								35000
EC6015H12S								25000
EC6015H12E								40000
EC6015M12B	12	0.08	0.96	4000	14.28	0.12	<29	50000
EC6015M12C								35000
EC6015M12S								25000
EC6015M12E								40000
EC6015L12B	12	0.07	0.84	3500	12	0.07	<27	50000
EC6015L12C								35000
EC6015L12S								25000
EC6015L12E								40000
EC6015LL12B	12	0.06	0.72	3000	11.33	0.06	<24	50000
EC6015LL12C								35000
EC6015LL12S								25000
EC6015LL12E								40000
EC6015TH24B	24	0.15	3.6	5500	20.73	0.2	<39	50000
EC6015TH24C								35000
EC6015TH24S								25000
EC6015TH24E								40000
EC6015HH24B	24	0.13	3.12	5000	19.42	0.18	<37	50000
EC6015HH24C								35000
EC6015HH24S								25000
EC6015HH24E								40000
EC6015H24B								50000

EC6015H24C	24	0.11	2.64	4500	18.12	0.16	<32	35000
EC6015H24S								25000
EC6015H24E								40000
EC6015M24B	24	0.09	2.16	4000	14.28	0.12	<29	50000
EC6015M24C								35000
EC6015M24S								25000
EC6015M24E								40000
EC6015L24B	24	0.07	1.68	3500	12	0.07	<27	50000
EC6015L24C								35000
EC6015L24S								25000
EC6015L24E								40000

**E--EL bearing, B -- Two ball bearing , C -- One ball One sleeve bearing, S -- Sleeve bearing**