

Model Type : EC-6020xxxx  
 Dimension :60 x 60 x 20 mm



Voltage	5V		12V		24V
			✓		✓
Fan Speed	LL	L	M	H	HH
	3000	3500	4000	4500	5000
Certificate	UL		CE		TUV
	✓		✓		✓
Bearing Type	Sleeve		1 Ball	2 Ball	EL
	✓		✓	✓	✓

Model	Voltage VDC	Current AMP	Input Watts	Fan Speed RPM	AirFlow CFM	Pressure InchH <sub>2</sub> O	Noise dBA	Life Hour
EC6020M12B	12	0.17	2.04	4000	17.6	0.11	<26	50000
EC6020M12C								35000
EC6020M12S								25000
EC6020M12E								40000
EC6020L12B	12	0.14	1.68	3500	16.19	0.1	<23	50000
EC6020L12C								35000
EC6020L12S								25000
EC6020L12E								40000
EC6020HH24B	24	0.18	4.32	5000	23.64	0.2	<34	50000
EC6020HH24C								35000
EC6020HH24S								25000
EC6020HH24E								40000
EC6020H24B	24	0.15	3.6	4500	22.04	0.17	<30	50000
EC6020H24C								35000
EC6020H24S								25000
EC6020H24E								40000
EC6020M24B	24	0.12	2.88	4000	17.6	0.11	<26	50000
EC6020M24C								35000
EC6020M24S								25000
EC6020M24E								40000
EC6020L24B	24	0.09	2.16	3500	16.19	0.1	<23	50000
EC6020L24C								35000
EC6020L24S								25000
EC6020L24E								40000
EC6020LL24B	24	0.07	1.68	3000	13.88	0.07	<19.6	50000
EC6020LL24C								35000
EC6020LL24S								25000
EC6020LL24E								40000

**E--EL bearing, B -- Two ball bearing, C -- One ball One sleeve bearing, S -- Sleeve bearing**