


Model Type: EC-12038xxxx

Dimension : 120 x 120 x 38 mm

	Voltage	5V	12V		24V
				✓	✓
	Fan Speed	L	M	H	HH
		2000	2300	2600	2900
	Certificate	UL	CE		TUV
		✓	✓		✓
	Bearing Type	Sleeve	1 Ball	2 Ball	EL
		✓	✓	✓	✓

Model	Voltage VDC	Current AMP	Input Watts	Fan Speed RPM	AirFlow (Max) CFM	Pressure InchH ₂ O	Noise dBA	Life Hour
EC12038H12B	12	0.58	6.96	2600	92.49	0.22	<41	50000
EC12038H12C								35000
EC12038H12S								25000
EC12038H12E								40000
EC12038M12B	12	0.4	4.8	2300	79.9	0.17	<38	50000
EC12038M12C								35000
EC12038M12S								25000
EC12038M12E								40000
EC12038L12B	12	0.37	4.44	2000	72.5	0.14	<34	50000
EC12038L12C								35000
EC12038L12S								25000
EC12038L12E								40000
EC12038HH24B	24	0.46	11.04	2900	107.49	0.26	<45.8	50000
EC12038HH24C								35000
EC12038HH24S								25000
EC12038HH24E								40000
EC12038H24B	24	0.42	10.08	2600	92.49	0.22	<41	50000
EC12038H24C								35000
EC12038H24S								25000
EC12038H24E								40000
EC12038M24B	24	0.34	9.12	2300	79.9	0.17	<38	50000
EC12038M24C								35000
EC12038M24S								25000
EC12038M24E								40000
EC12038L24B	24	0.34	8.16	2000	72.5	0.14	<34	50000
EC12038L24C								35000
EC12038L24S								25000
EC12038L24E								40000

E--EL bearing, B -- Two ball bearing , C -- One ball One sleeve bearing, S -- Sleeve bearing