


**▼NFR SERIES(EMI SUPPRESSION CORES WITH PLASTIC CASE)****1.ORDERING CODE**

K1   NFR   -08   BK   2

\_\_\_\_\_ FLAMMABILITY(UL 94V-2)  
\_\_\_\_\_ COLOR(BK:BLACK;IV:IVORY)  
\_\_\_\_\_ SERIES NUMBER  
\_\_\_\_\_ TYPE  
\_\_\_\_\_ MATERIAL

**2.SHAPES**



**3.DIMENSIONS**

Unit:mm

NO.	FERRICO PART NO.	Fig.	ΦA	B	ΦC	D	E	CABLE DIAMETER	IMPEDANCE(Ω) TYP.	
									25 MHz	100 MHz
1	<u>K1 NFR-08-A</u>	1	19.5±1.0	24.0±1.0	8.0±1.0	17.0±1.0	22.5±1.0	MAX.Φ 7.5	61	113
2	<u>K1 NFR-08A</u>	2	19.2±1.0	22.8±1.0	8.1±1.0	19.8±1.0	25.9±1.0	MAX.Φ 7.5	57	145
3	<u>K1 NFR-10</u>	3	23.6±1.0	28.0±1.0	10.0±1.0	13.6±1.0	19.6±1.0	MAX.Φ9.5	45	100
4	<u>K1 NFR-12</u>	3	27.5±1.0	32.0±1.0	12.0±1.0	17.5±1.0	23.5±1.0	MAX.Φ11.5	68	132
5	<u>K1 NFR-14</u>	4	29.5±1.0	34.0±1.0	14.0±1.0	15.5±1.0	21.5±1.0	MAX.Φ13.5	45	95

**REMARK: OTHER SIZE ARE AVAILABLE UPON REQUEST**