



6W

VT-816 6W LED WALL LIGHT COLORCODE:3000K -BLACK BODY

Lumens 660	Beam Angle 350	Dimensions 110x54x97mm
----------------------	--------------------------	----------------------------------

Warm White
 SKU:8288

2 YEARS
 WARRANTY

SENSOR
 COMPATIBLE



Technical Information

Instant Start:	0-100% in 1/1s
Watts:	6
Lumens:	660
Beam Angle:	350
Unit Color:	Black
Body Type:	Aluminium
Long life:	20,000 Hours
LED Chip Type:	SMD

IP Rating:	IP65
Dimmable:	No
Warranty (Years):	2
PF:	>0.5
CRI:	>80
Operation Temperature:	-20 to +45°C
Input Power:	AC:220-240V,50/60 Hz
Sensor Compatibility:	Yes

Features

- ✓ Designed for perfection - 360 Rotatable wall light
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Available in different unit_colors and color temperature options - Warm White and Day White
- ✓ Excellent heat dissipation
- ✓ Easy installation and Maintenance
- ✓ Applications - Perfectly suitable for Indoor and Outdoor applications

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.59
Unit CBM	0.00072

Listing Details

EAN Code	3800157629829
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	1120

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES