


P.C.B LAYOUT
BOTTOM VIEW



SCHEMATIC (NON-SHORTING)

Rating	DC 50V 0.5A
Circuit	1P - 2T
Timing	Shorting
Contact Resistance	200mΩ Max.
Insulation Resistance	100MΩ Min.
Operating Force	250gf ±100gf
Operating Life (cycle)	10,000 Min.

9.0mm
8.0mm
7.0mm
6.0mm
5.0mm
4.0mm
3.0mm
2.0mm
G (mm)

NO.	PARTS	MATERIALS	Q'TY	FINISH
6	SPRING	STEEL WIRE	1	NATURAL
5	CONTACT	BRASS STRIP	1	Ag PLATED
4	TERMINAL	BRASS STRIP	3	Ag PLATED
3	CASE	PHENOLIC RESIN	1	NATURAL
2	FRAME	STEEL STRIP	1	Ni PLATED
1	KNOB	POM	1	BLACK

>0.5~2	±0.05	±0.10	±0.15
>2~5	±0.15	±0.20	±0.25
>5~10	±0.25	±0.28	±0.30
角度 ANGLE	±0.5°		
注：“*”表示关键尺寸(5个)			

第一视角	设计 Jack Jin	图面 单位	A4 MM	东莞市美韩电子科技有限公司 Dongguan Usakro Electronic Technology Co., Ltd.		
	审核 Jacky Zhong	比例 重量		1:1	DWG NO.	型号:SS-12F44-G3
	批准 Tony Meng	页码 版次	1/1 A/0	1 of 1	PART NO.	规格:12.1*5.6*13.9
						SIZE A4 VER R