





DIMENSIONS




SCHEMATIC



Rating	0.3A 50V DC
FUNCTION	1P2T
Contact Resistance	200mΩ Max.
Insulation Resistance	100MΩ Min.
Operating Force	200gf ± 80gf
Operating Life	10,000 cycle



P.C.B MOUNTING PATTERN



Model No.	G (mm)
SS-12D01-G2	2mm
SS-12D01-G3	3mm
SS-12D01-G4	4mm
SS-12D01-G5	5mm
SS-12D01-G6	6mm
SS-12D01-G7	7mm
SS-12D01-G8	8mm
SS-12D01-G9	9mm

NO.	DESCRIPTION	QTY	MATERIAL	REMARK
5	CONTACT(CLIP)	1	BRASS	Ag-Plated
4	TERMINAL	3	BRASS	Ag-Plated
3	TERMINAL BASE	1	PHENOL IC RESIN	Natural
2	FRAME	1	SPCC	Ni-Plated
1	KNOB	1	POM	Black

>0.5~2	±0.05	±0.10	±0.15
>2~5	±0.15	±0.20	±0.25
>5~10	±0.25	±0.28	±0.30
角度 ANGLE	±0.5°		
未注尺寸公差(mm)			

第一视角	设计	图面	A4	东莞市美韩电子科技有限公司		
	Jack Jin	单位	MM	Dongguan Usakro Electronic Technology Co., Ltd.		
	审核	比例		1:1	DWG NO.	型号: SS-12D01-G4
	Jacky Zhong	重量		1 of 1	PART NO.	规格: 8.8*3.9*4.0 直插1P2T
	批准	页码	1/1			SIZE
	Tony Meng	版次	A/0			A4
						VER
						R