



# DRC26-50S04 Product Details

[Share](#) | [Print](#) | [Email](#)


✔ **Active**  
[View 3D PDF](#)

## DRC Series Rectangular Connectors

50P PLUG ASM

**DRC26-50S04** ✔

TE Internal Number: DRC26-50S04

**Product Highlights** [View All](#)

- DRC Product Line
- Wire-to-Wire
- Applies To Plug
- Connector
- Plug

- [Pricing & Availability](#) ➤
- [Request Sample](#) ➤
- [Add to My Part List](#) +
- [Buy Product through Distributor](#) ➤

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

Product Type Features	
Product Line	DRC
Product Type	Connector
Connector Type	Plug
Wire Insulation Diameter (mm [in])	2.54 - 3.40 [0.100 - 0.134]
Wire/Cable Type	SXL, GXL & TXL
Sealed	Yes

Mechanical Attachment	
Contact Retention	With
Contact Retention Type	Retainer
Mating Retention Type	Jackscrew(s)

Electrical Characteristics	
Contact - Rated Current (A)	7.5
Operating Voltage Reference	DC
Operating Voltage (VDC)	250

Termination Features	
Wire/Cable Size (mm <sup>2</sup> )	0.5 - 2
Wire/Cable Size (AWG)	14 - 20
Termination Method to Wire/Cable	Crimp
Seal Type	Grommet

Body Features	
Wire Type	Stranded
Cable Exit Angle	180°
Mating Retention	With

Contact Features	
Contact Type	Socket
Contact Layout	In-Line
Contact Base Material	Copper Alloy
Contact Plating, Mating Area, Material	Nickel over Copper
Contact Qty Size 20	50

Housing Features	
Housing Material	Thermoplastic
Housing Color	Black
Mating Alignment Type	Keyed
Mating Alignment	With

Configuration Features	
Number of Positions	50
Strain Relief	Optional

Industry Standards	
UL Flammability Rating	UL 94V-0
RoHS/ELV Compliance <span style="font-size: small;">?</span>	RoHS compliant, ELV compliant
RoHS/ELV Compliance History	Always was RoHS compliant

Identification Marking	
Keying	With

Environmental	
Operating Temperature (°C [°F])	125 [257]

Conditions for Usage	
Applies To	Plug

Operation/Application	
Application Use	Wire-to-Wire
Contact Transmits (Typical Application)	Signal/Power
Industry Application	Harsh Environment/Industrial

Other	
Industry	Industrial-Commercial & Building Equip
Brand	DEUTSCH

**Related Products**

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

**Corporate Information**

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

**Quick Links**

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

**Customer Support**

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

**Keep Me Informed**