

RJ45 bending protection sleeve - VS-08-KS-H/GN - 1654756

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

RJ45 bend protection sleeve, for pin inserts VS-08-ST-H11-RJ45 and VS-08-ST-H21-RJ45, for cable cross section up to 7 mm, color: green



Ethernet

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	5 pc
Weight per Piece (excluding packing)	2.28 g
Custom tariff number	39269097
Country of origin	China

Technical data

Mechanical characteristics

External cable diameter	7 mm
Color	green

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Degree of protection	IP20

Material data

Flammability rating according to UL 94	V0
Housing material	PA

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

RJ45 bending protection sleeve - VS-08-KS-H/GN - 1654756

Classifications

eCl@ss

eCl@ss 4.0	27140906
eCl@ss 4.1	27140906
eCl@ss 5.0	27140915
eCl@ss 5.1	27140915
eCl@ss 6.0	27140915
eCl@ss 7.0	27439224
eCl@ss 8.0	27440212

ETIM

ETIM 2.0	EC000307
ETIM 3.0	EC001680
ETIM 4.0	EC001680
ETIM 5.0	EC001680

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted


Approval details

EAC

RJ45 bending protection sleeve - VS-08-KS-H/GN - 1654756

Drawings

Dimensional drawing



RJ45 bending protection sleeve