

**Stego, Inc.**

1395 South Marietta Parkway


Building 800

Marietta, GA 30067, USA

Toll-Free: (888) 783-4611 • **Phone:** (770) 984-0858**Fax:** (770) 984-0615**Email:** info@stegousa.com • **Website:** www.stegousa.com

[All Categories](#) > [Heating](#) > [Fan Heaters](#) > [CR 027 - PTC Fan Heater](#) > Part # 02700.0-00

Part # 02700.0-00, PTC Fan Heater



[Specifications](#) | [Technical Data](#)

Specifications

Power ¹	475 W
Voltage	220 - 240 VAC
Max. Current	11 A (inrush)
Thermostat Range	0 to 60 °C
Fan	On/off with heater
Agency Approvals	UL, VDE

Technical Data

Heating Element	PTC resistor, temperature limiting
Overheat Protection	built-in temperature limiter
Housing	Plastic, UL 94V-0, light gray
Axial Fan, Ball Bearing	50,000 h at 77 °F (25 °C)
Air Flow, Free Blowing	20 cfm (35 m ³ /h)
Function Control Light	LED
Connection	2-pole terminal, AWG 14 max (2.5 mm ²)
Mounting	Clip for 35 mm DIN rail (EN 60 715)
Position	Preferably vertical
Dimensions	6.5 x 3.94 x 5.0 inches (165 x 100 x 128 mm)
Weight	2.0 lb (900 g)
Operating/Storage Temperature	-49 to 158 °F (-45 to 70 °C)
Protection Type	IP20
Protection Class	II (double insulated)

¹ at 68 °F (20 °C) ambient temperature. Also, power will vary when frequency other than listed is applied (see Heating Power curves).