

SSR21NVS-M10345

Aliases (UALS21V1034500)

KEMET, SSR21NVS-M/NHS-M, AC Line Filters, Common Mode, 34.5 mH



Click [here](#) for the 3D model.

Dimensions

L	22mm MAX
T	16mm MAX
H	27mm MAX
LL	3.5mm +/-0.5mm
S	13mm +/-0.5mm
S1	10mm +/-0.5mm
Wire Size	0.32mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	450
Component Weight	13 g

General Information

Series	SSR21NVS-M/NHS-M
Style	Through-Hole
Features	High Performance, High Impedance, Strong Inductance
RoHS	Yes
Miscellaneous	60 (K) Temperature Rise Max.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	34.5 mH (10 kHz)
Current	1 A
Temperature Range	-25/+120°C
DC Resistance	510 mOhms