

**MTS 1-PHASE SAFETY TRANSFORMER**

P: 160VA IN: 230/400VAC OUT: 24VAC

Single-phase safety transformer  
160 VA  
Isolation class T 40/B  
Other voltages on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Approvals****General data**

Standards	EN 61558-1, EN 61558-2-6, EN 62041 category 0
Test isolation voltage	4 kV (prim./sec.)
Mounting method	Long-hole mounting or DIN-rail mountable TH35 (EN 60715)
Temperature range	-20...+40 °C (storage temperature -40...+80 °C)
Dimensions H×W×D	101×96×106 mm
Fixing centers a×b×c	86.5×84×4.8 mm
Drill hole Ø	4.8×8.4 mm

**Output**

Output voltage	24 V AC (SELV)
Output rating	160 VA



**Input**

Input voltage	230/400 V AC
Frequency	50...60 Hz
Input current	0.82 A (230 V AC); 0.47 A (400 V AC)
Inrush current	6.1 A (230 V AC); 3.5 A (400 V AC)
Short-circuit current	9.5 A (230 V AC); 5.5 A (400 V AC)

**Commercial data**

country of origin	CZ
customs tariff number	85043180

EAN	4048879078528
eClass	27031302
Packaging unit	1

**Sketch**

Product may differ from Image