



To: NKK Authorized Distributor/Representative

Date: 11/19/2020

**Re: New Product Announcement:
KP01 Pushbutton with Rectangular Cap and RGB LEDs**

NKK is pleased to announce a new offering from our renowned KP Series. This new illuminated push-button offers the same exceptional quality and performance but is accentuated by a rectangular cap and RGB LEDs. Each switch and cap assembly has three LEDs to produce brilliant, seamless illumination and limitless color possibilities. The single pole momentary device has crisp, tactile actuation, gold contacts and straight PC terminals. The unique rectangular cap is slightly sculptured and complements any control panel configuration. Legend options may be printed on cap lens or film insert.

See the following for part number, description and features.

Part Number	Switch Description	Features
KP0115ACBKG03RGBJB	Electrical Capacity: 100mA maximum @ 12V DC Gold Contacts & Straight PC Terminals Pole & Circuit: SPST OFF (ON) Mechanical Life: 1,000,000 Operations Minimum Electrical Life: 1,000,000 Operations Minimum Total Travel: .177" (4.5mm) Operating Temperature Range: -25°C ~ +50°C (-13°F ~ +122°F)	Cap Size: 34.8mm L x 17.4mm W x 17.5mm H (1.370" x .685" x .689") Three RGB LEDs Produce Brilliant Illumination Smooth and Evenly Distributed LED Radiance Clear Lens & White Diffuser Moderately Sculptured Surface Provides Ease of Actuation Generous Cap Surface Perfect for Legends

KP0115ACBKG03RGBJB

Switch & Cap Assembly

The LED in the center of the switch bottom is an integral part of the switch. Two other RGB LEDs and two spacers are packaged separately. Custom legend services available.

Target Applications

- Transportation
- Military
- Stage / Lighting Control Panel
- Audio / Broadcast



For product samples, please contact

NKK Customer Service at CustomerService@nkkswitches.com or call 480.991.0942