



Power cable

Model: **AK-NB-01C**



Product code	AK-NB-01C
Product type	Power cable
Series	Copper
Output voltage	250 V
Output amperage	2.5 A
Ground wire	Yes
Cable length	1.5 m
The cable plug #1	Hybrid standard C/E/F (CEE 7/7)
The cable plug #2	IEC C5
Material	Oxygen-free copper 4N (99.99%)
Wire construction	3 x 0.75 mm ²
Isolation material	PVC
Cable diameter	7 mm
Product color	Black
Product size (L x W x H)	210 x 70 x 50 mm
Net weight	340 g
CE compatibility	Yes
FCC compatibility	No
RoHS compatibility	Yes
REACH compatibility	Yes
EAN code	5901720131478
Warranty	24 months



Description

High-quality 3-pin power cable „clover” type Pro Akyga® AK-NB-01C, with a length of 1.5 m.

The cord is made of oxygen-free copper (OFC) in 99.99 %, which ensures long-term durability of the product without losing its properties. Designed to power notebook internal power supplies and all other compatible with IEC C5 plug.

Product is compatible with most power supplies available in Akyga's offer.