

datasheet for MPK 1
article number: 930268100

product description:	order number: 930 268-100
description:	2 mm diameter miniature pole clamp with transverse hole, insulated, goldplated copper beryllium contact spring, tin-plated brass threaded bolt with solder connection. Suitable for installation in equipment chassis and switch panels up to a maximum wall thickness of 3.5 mm.
typ:	MPK 1 schwarz/black
system:	2 mm system
order number:	930 268-100
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	spring-loaded socket ? 2 mm, cross hole ? 2 mm
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	6 A
Please consider derating curve!	
contact resistance:	6 mOhm
material	
contact material:	contact spring: copper - beryllium
contact surface material:	gold
housing material:	PA
environmental conditions:	
temperature range:	-20 °C to +60 °C
drawing	