

Professional electric diagonal cutters with DynamicJoint® 160 mm, 6 1/2" (43335)



Tools that work for you

Wiha Werkzeuge GmbH
Obertalstraße 3-7 78136 Schonach
E-Mail: info.de@wiha.com
Tel.: +49 (0)7722 959-0



Order no.: 43335

Article number: Z12116006

EAN: 4010995433352

Customs tariff number: 82032000

Protects your health: Special DynamicJoint® design reduces effort required for cutting.
Lowers your costs: Durable thanks to high-quality, chrome-plated plier surface to prevent corrosion.
Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.
Application: For cutting cables as well as soft and hard wires. For working on live parts up to 1,000 V AC.
A tradesman's tool kit would be incomplete without a universal cutter to cut hard and soft wires. The diagonal cutters Professional electric by Wiha prove themselves to be robust, all-rounder pliers. The plier joint with DynamicJoint® ensures hand force is optimally applied when cutting, providing up to 40% greater cutting force. With their semi-circular head, these precision pliers also provide a clean cut edge. The ergonomically shaped plier handle ensures comfortable, fatigue-proof work. The high-quality chrome-plated plier surface also provides protection against rust, ensuring the pliers have a long service life. These diagonal cutters are also manufactured as per the international IEC 60900 standard and are thus approved for working on live parts up to 1,000 V AC.
Manufactured acc. to IEC 60900.

Customs tariff number	82032000
-----------------------	----------

Blister packed	No
----------------	----

Durchmesser max	2 mm
-----------------	------

Cutting force	16
---------------	----

Overall length (mm)	160 mm
---------------------	--------

Overall length (Inch)	6 1/2"
-----------------------	--------

VDE article	Yes
-------------	-----

Country of origin (ISO 3166-1 Alpha 3)	VNM
--	-----
