

<b>PART NAME</b>	NON-METALLIC ENCLOSURE (STYLE D)	<b>PART No.</b>	NBD-10452 & NBD-10472 & NBD-15452
------------------	----------------------------------	-----------------	-----------------------------------

**MATERIAL:**

INDOOR VERSION  
 SOLID BODY & COVER \_\_\_\_\_ ABS/PC BLENDED PLASTIC  
 UL94-5VB FLAMMABILITY RATING

CLEAR COVER \_\_\_\_\_ POLYCARBONATE PLASTIC  
 UL94V-0 FLAMMABILITY RATING  
 UV STABILIZED

OUTDOOR VERSION  
 SOLID BODY & COVER \_\_\_\_\_ PBT/PC BLENDED PLASTIC  
 UL94-5VA FLAMMABILITY RATING  
 UV STABILIZED

**FINISH:**  
 BODY \_\_\_\_\_ LIGHT GRAY  
 COVER \_\_\_\_\_ LIGHT GRAY OR CLEAR


COVER INCLUDES GRAY POLY-URETHANE GASKET.

AIR AND MOISTURE VENTS, STAINLESS STEEL LOCKING HASP, PANEL MOUNTING RAILS, GALVANIZED STEEL INNER PANEL AND STAINLESS STEEL WALL MOUNTING BRACKETS ARE NOT INCLUDED, BUT CAN BE PURCHASED SEPARATELY.

**INDUSTRY STANDARDS:**

INDOOR VERSION  
 UL508 TYPE 1, 2, 4, 4X INDOOR, 12 & 13  
 NEMA TYPE 1, 2, 4, 4X, 12 & 13  
 IEC529-IP65

OUTDOOR VERSION  
 UL508 TYPE 1, 2, 4, 4X, 12 & 13  
 NEMA TYPE 1, 2, 4, 4X, 12 & 13  
 IEC529-IP65



INDOOR VERSION		OUTDOOR VERSION	<b>NOTE:</b> ALL DIMENSIONS HAVE ±0.039 [±1] TOLERANCE UNLESS OTHERWISE SPECIFIED																			
PART NO.		PART NO.	DIMENSIONS = INCHES [MILLIMETERS]																			
SOLID COVER	CLEAR COVER	SOLID COVER	DIMENSIONS																			
A	B	C	D	E	F	G	H	J	K	L	M	N	P	R	S	T	U	V	W			
NBD-10452	NBD-10472	NBD-15452	11.024 [280]	10.200 [259]	10.038 [255]	8.850 [225]	8.253 [210]	6.902 [175]	14.961 [380]	14.135 [359]	13.987 [355]	12.795 [325]	12.212 [310]	10.833 [275]	3.855 [98]	3.151 [80]	14.870 [378]	14.753 [375]	10.937 [278]	10.835 [275]	13.404 [340]	9.476 [241]

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[NBD-10472](#)