


ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
	C	ECR # 061123-5 ADD LENGTH	11/23/06
	D	ECR # 061218-6 ADD CABLE P/N	12/18/06



NOTE:

- CABLE: UL 2919[30AWG(7/0.102 T.C)*1C INS: FOAM-PE ID:1.3±0.05 + SPIRAL(T.C)]*3C INS: PVC ID:2.3±0.1+28AWG(7/0.127 T.C)*7C + INS:SR-PVC ID:ø0.9±0.05mm+AL/MY+DRAIN 30AWG(7/0.102 T.C) + BRAID (16/4/0.1 T.C)+OUTER JACKET: PVC COLOR: BLACK(NK-K01) OD:ø7.5±0.15mm, **(C2919283BA)**
- CONNECTOR:
P1&P2: HDB 15P MALE, GOLD FLASH CONTACT, NICKEL PLATED SHELL.
9TH PIN IS EMPTY.
- FERRITE CORE: 17.5*28.5*9.5mm.
- SHIELD: COPPER-FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE BRAID.
- HOOD: MOLDED TYPE, PVC 45P, COLOR: BLACK(NK-K01).
- ELECTRICAL TEST: 100% OPEN SHORT MIS WIRE TEST . CONTACT RESISTANCE 3Ω MAX
INSULATION RESISTANCE 10MΩ MIN
- PACKING: <1>EACH PC / POLYBAG + EAN CODE LABEL & ROHS LABEL
<2>EACH CARTON / ROHS LABEL(L*W=35*22mm)

PIN OUT		P1		P2	
1		1	ORANGE	10	WHITE
2		2	YELLOW	11	YELLOW
3		3	GREEN	12	GREEN
4		4	RED	13	RED
5		5	BRAID	14	SHELL
			CENTER		
			SHIELDING		

120-2620-6	CY0018	20000±200mm	4260113562994	
120-2620-5	CY0017	15000±150mm	4260113562512	
120-2620-4	CY0016	10000±100mm	4260113562505	
120-2620-3	CY0003	5000±50mm	4260113560204	
120-2620-2	CY0002	3000±30mm	4260113560198	
120-2620-1	CY0001	1800±30mm	4260113560181	
DWG	P/N	L±T	EAN CODE	

Tolerance Inch M/M		Title	
X	.015	.30	2DIRECT GMBH
.XX	.010	.10	
.XXX	.005	.05	
Draw	Customer P/N		HDB 15M/M CABLE
FANNIE 12/18/06			
App'd	Customer	E-DIR	
Scale	NONE	Units	m/m Third Angle Projection
Dwg No.	120-2620	REV:ID	Sheet 1/2