




HONEYWELL PART NUMBER
413SX21-T
PRODUCT CODE VDX1321
MILITARY PART NUMBER M8805/106-02

REV	DOCUMENT	CHANGED BY	CHECK
3	0038558	SS 08MAY08	BLR



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
- 2 TERMINALS ARE PLATED FOR SOLDERING
- 3 SWITCH WILL WITHSTAND TEMPERATURE OF 400°F
- 4 MOVABLE CONTACT MATERIAL - 24K SOLID GOLD OVERLAY
- 5 STATIONARY CONTACT MATERIAL - GOLD ALLOY

RELEASE NO.	PR-10353
REPLACES	

CHARACTERISTICS
OPERATING FORCE----- 5 OZ MAX
RELEASE FORCE----- 1 OZ MIN
DIFFERENTIAL TRAVEL -- .002 MAX
OVERTRAVEL ----- .004 MIN

ELECTRICAL DATA
CONTACT ARRANGEMENT SPDT

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES ±

DRAWN	SPK	29FEB08
CHECK	RJ	29FEB08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	413SX21-T	3
SCALE	-	WEIGHT: .003 LB MAX	SHEET 1 OF 1

APPROVALS		
MILITARY	M8805/106-02	BRAND

