


PCB LAYOUT



P/N LEGEND

A1501 WR-S-XP
① ② ③ ④

- ① Series No.
- ② Connector type: WR=Right angle
- ③ Mounting type: S=SMT
- ④ No. of circuits

SPECIFICATIONS

Current Rating: 3A AC,DC
 Voltage Rating: 350V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 20mΩ Max.
 Insulation Resistance: 1000MΩ Min.
 Withstanding Voltage: 500V AC/minute
 Pin Material: Brass/Tin-plated
 Material: Nylon 6T,UL94V-0
 Color: Natural(Beige)

PART NO.	Dimensions	
	A	B
02P	1.50	4.30
03P	3.00	5.80
04P	4.50	7.30
05P	6.00	8.80
06P	7.50	10.30
07P	9.00	11.80
08P	10.50	13.30
09P	12.00	14.80
10P	13.50	16.30
11P	15.00	17.80
12P	16.50	19.30
13P	18.00	20.80
14P	19.50	22.30
15P	21.00	23.80

 燦達電子工業股份有限公司
 JOINT TECH ELECTRONIC IND. CO., LTD.

UNIT	SCALE	SHEET
mm	1 : 1	1 of 2
DRAWN BY	APPROVED BY	
唐騰風	張子波	
2013. 10. 17	2013. 10. 17	
GENERAL TOLERANCE		
B3	EN1403100004	2014. 02. 14 周傑亮
B2	EN1312190439	2013. 12. 19 唐騰風
B1	REVISE	2006. 04. 13 蕭惠鳳
B0	NEW RELEASE	2006. 04. 13 蕭惠鳳
REV.	DESCRIPTION	DATE NAME
	X. X±0.25	ANGLE±
	X. XX±0.15	
	X. XXX±0.05	

TITLE:
 1.50mm PITCH
 90° WAFER-SMT TYPE

DRAW NO. : A1501WR-S-XP REV. B3