



Part Number : [1201010002](#)


Product Description : PROFIBUS Data Line
Micro-Change (M12) Tee, 5 Poles,
Male/Female with Male Drop

Series Number : 120101

Status : Active

Product Category : Industrial Tees and
Splitters

Engineering Number : PDTS01




Documents & Resources

Drawings

[Drawing 1201010002_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/108/2014 (17 Dec 2014)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120101
Description	PROFIBUS Data Line Micro-Change (M12) Tee, 5 Poles, Male/Female with Male Drop
IP Rating	IP67
Product Name	PROFIBUS Data Line
Type	Drop Tee
UPC	78678853913

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC/DC

Physical

Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	Single
LED Indicator	No
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Male
Leg 1 Length	N/A
Leg 2 Length	N/A
Length	0.066m
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	1548.130/g
Poles	5
Right Trunk Connector	Micro-Change (M12)

Right Trunk Gender	Female
Temperature Range - Operating	-20°C to +80°C

This document was generated on Mar 23, 2024