



Part Number : [1300150109](#)

Product Description : Mini-Change C-Size Receptacle, 19 Poles, 1/2" - 14 NPT Threads, Male (Straight) to Leads, 0.30m (11.81") Length

Series Number : 130015

Status : Active

Product Category : Circular Industrial Connectors

Engineering Number : 3R3N36E80C300



Documents & Resources

Drawings

[Drawing 1300150109_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130015
Description	Mini-Change C-Size Receptacle, 19 Poles, 1/2" - 14 NPT Threads, Male (Straight) to Leads, 0.30m (11.81") Length
Comments	C-Size (1-1/8" - 16 UN-2A)
IP Rating	IP67
Product Family	Brad Mini-Change Connectors
Product Name	Mini-Change
Type	Single Ended (pigtail)
UPC	78678841464

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	300V AC/DC

Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	0.30m
Material - Component	Gray Anodized Aluminum
Mounting Thread Size	PG16
Net Weight	82.300/g
Orientation	Straight
Panel Mount	Front
Poles	19
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	UL 1569

Wire Size (AWG)	18, 22
-----------------	--------

This document was generated on Mar 23, 2024