



Part Number : [1300660083](#)


Product Description : BradPower A-Size (7/8"-M22) Receptacle, 4 Poles, Male, 1/2" - 14 NPT, 14/1 AWG, 0.305m (1.0') Length

Series Number : 130066

Status : Active

Product Category : Circular Industrial Connectors

Engineering Number : 1R4006A28A120G




Documents & Resources

Drawings

[Drawing 1300660083_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Cadmium-chloride; Lead; α,α -Bis[4-(dimethylamino)phenyl]-4-(phenylamino)naphthalene-1-methanol [with $\geq 0.1\%$ of Michler's ketone (EC no. 202-027-5) or Michler's base (EC no. 202-959-2)]... per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130066
Description	BradPower A-Size (7/8"-M22) Receptacle, 4 Poles, Male, 1/2" - 14 NPT, 14/1 AWG, 0.305m (1.0') Length
IP Rating	IP67
Product Family	BradPower Cordsets and Receptacles
Product Name	BradPower A-Size
Type	Single Ended (pigtail)
UPC	78678856582

Agency

UL	E258922
----	---------

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	600V

Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	0.305m
Material - Component	Zinc Die-Cast with Black Epoxy
Mounting Thread Size	1/2" - 14 NPT

Net Weight	222.000/g
Orientation	Straight
Panel Mount	Front
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 1015
Wire Size (AWG)	14

This document was generated on Mar 23, 2024