



BFG.2B.100.PCSG

MECHANICAL DETAILS

Shell Style Model BFG* : Plug cap


Keying 1 key (alpha=0, plug: male contacts, receptacle: female contacts)

Housing Material POM (Polyoxymethylene) shell without treatment, silicone gasket

Cable Fixing 0 - 0 mm

Variant 2 :

	Col	Col	Col	Col	Col	Col	Col	Col
Mm.								
In.								



Available Download

unipole_multipole.pdf

PERFORMANCE DETAIL

Insert :

Insulator

Insulator



OTHER CHARACTERISTICS

Shell Style/Model Libellé

Temp (min) -55°C

Temp (max) +250°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms]

Salt Spray >144 hr

Climatical 50/175/21

Shielding (min): 75 dB (10 MHz)

Shielding (min): 40 dB (1 GHz)

IP Rating 50



Related links

- [Contact](#)
- [Quote Request](#)
- [Catalogs Downloads](#)
- [Catalogs Requests](#)
- [Sample Request](#)
- [3D drawings](#)