



**10W**

VT-830 10W LED WALL LIGHT COLORCODE:6400K WHITE BODY 25CM HEIGHT

Lumens <b>450</b>	Beam Angle <b>72</b>	Dimensions <b>108x250mm</b>
----------------------	-------------------------	--------------------------------

White  
 SKU:8318

**2 YEARS**  
 WARRANTY



## Technical Information

Watts:	10	IP Rating:	IP65
Lumens:	450	Dimmable:	No
On/Off Cycles:	>15000	Warranty (Years):	2
Beam Angle:	72	PF:	>0.5
Unit Color:	White	CRI:	>80
Body Type:	Aluminium	Operation Temperature:	-20 to +45°C
Long life:	20,000 Hours	Input Power:	AC:100-240V,50/60Hz
LED Chip Type:	COB(CREE)		

## Features

- ✓ Perfect replacement for traditional fittings as they are more flexible & efficient
- ✓ Works perfectly in extreme temperatures from -20° to 50 without any adverse effects
- ✓ Specifically designed for Outdoor use
- ✓ IP65/67 Protection Rating to ensure safety
- ✓ Used for Gardens, Outdoor Residential Areas, Walkways & Passages, Driveways, Fountains, Lawns, Entrance, Patio or Terrace and similar environments

# Packaging

## Unit Details

Gross Weight(GW) Kgs	1.16
Unit CBM	0.00918

## Listing Details

EAN Code	3800157632294
Commodity Code	9405403990

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	8
Qty Per Pallet	120

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES