



10W

VT-820 10W LED WALL LIGHT COLORCODE:6400K WHITE BODY 80CM HEIGHT

Lumens 450	Beam Angle 72	Dimensions 108x800mm
----------------------	-------------------------	--------------------------------

White
 SKU:8327

2 YEARS
 WARRANTY



Technical Information

Watts:	10	IP Rating:	IP65
Lumens:	450	Dimmable:	No
Beam Angle:	72	Warranty (Years):	2
Unit Color:	White	PF:	>0.5
Body Type:	Aluminium	CRI:	>80
Long life:	20,000 Hours	Operation Temperature:	-20 to +45°C
LED Chip Type:	COB(CREE)	Input Power:	AC:100-240V,50/60Hz

Features

- ✓ Perfect replacement for traditional fittings as they are more flexible & efficient
- ✓ Works perfectly in extreme temperatures from -20° to 50 without any adverse effects
- ✓ Specifically designed for Outdoor use
- ✓ IP65/67 Protection Rating to ensure safety
- ✓ Used for Gardens, Outdoor Residential Areas, Walkways & Passages, Driveways, Fountains, Lawns, Entrance, Patio or Terrace and similar environments

Packaging

Unit Details

Gross Weight(GW) Kgs	2.39
Unit CBM	0.02754

Listing Details

EAN Code	3800157632386
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	4
Qty Per Pallet	48

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES