



**12W**

VT-822 12W LED WALL LIGHT COLORCODE:4000K BLACK BODY

Lumens <b>750</b>	Beam Angle <b>140</b>	Dimensions <b>130x160mm</b>
----------------------	--------------------------	--------------------------------

Day White  
SKU:8341

**2 YEARS**  
WARRANTY



## Technical Information

Watts: <b>12</b>	Dimmable: <b>No</b>
Lumens: <b>750</b>	Warranty (Years): <b>2</b>
Beam Angle: <b>140</b>	PF: <b>&gt;0.5</b>
Unit Color: <b>Black</b>	CRl: <b>&gt;80</b>
Body Type: <b>PC</b>	Operation Temperature: <b>-20 to +45°C</b>
Long life: <b>20,000 Hours</b>	Input Power: <b>AC:100-240V,50/60Hz</b>
IP Rating: <b>IP65</b>	

## Features

- ✓ Perfect replacement for traditional fittings as they are more flexible & efficient
- ✓ Works perfectly in extreme temperatures from -20° to 50 without any adverse effects
- ✓ Specifically designed for Outdoor use
- ✓ IP65/67 Protection Rating to ensure safety
- ✓ Used for Gardens, Outdoor Residential Areas, Walkways & Passages, Driveways, Fountains, Lawns, Entrance, Patio or Terrace and similar environments

## Packaging

### Unit Details

Gross Weight(GW) Kgs 0.482

Unit CBM 0.002856

### Listing Details

EAN Code 3800157632522

Commodity Code 9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton) 20

Qty Per Pallet 400

READY STOCKS IN  
**UK & EU**



Dispatch within  
24 Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES