



VT-7614 GU10 GARDEN LAMP,ALUMINIUM BODY -BLACK IP54

Dimensions  
**80x80x500mm**

SKU:7564

**3 YEARS**  
WARRANTY



## Technical Information

Holder Type: **GU10**

Rated Load: **Max 35W**

Body Type: **Aluminium Body + Clear PC Diffuser**

IP Rating: **IP54**

Dimmable: **No**

Warranty (Years): **3**

Operation Temperature: **-20? to 45?**

Input Power: **AC:220-240V, 50/60Hz**

## Features

- ✓ Perfect replacement for traditional wall fittings
- ✓ Designed with an Ingress protection of IP54
- ✓ Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only - Light not included)
- ✓ Easy to Install and low maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

# Packaging

## Unit Details

Gross Weight(GW) Kgs	1.05
Unit CBM	0.004131

## Listing Details

EAN Code	3800157636377
Commodity Code	9405109890

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	4
Qty Per Pallet	288

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES