



6W

VT-756 6W-WALL LAMP WITH BRIDGELUX CHIP COLORCODE:3000k
WHITE ROUND

Lumens 660	Beam Angle 120	Dimensions 140x115x100mm
----------------------	--------------------------	------------------------------------

Warm White
SKU:7082

2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Instant Start: 0-100% in 11s

Watts: 6

Lumens: 660

Shape: Round

Beam Angle: 120

Unit Color: White

Body Type: Aluminium

Long life: 20,000 Hours

IP Rating: IP65

Dimmable: No

Warranty (Years): 2

PF: >0.45

CRI: >80

Operation Temperature: -25 to +50°C

Input Power: AC:220-240V,50/60Hz

Sensor Compatibility: Yes

Features

- ✓ High Quality Bridgelux chips for reliable operation and lifetime
- ✓ Get range of up-down beams with Adjustable beam angle to feel range of aesthetics
- ✓ Constructed to high quality aluminum for efficient heat dissipation
- ✓ Cylindrical & Cubical fixtures in 3 colors to fit into range of architectural structures
- ✓ Elegant replacement for traditional up-down lighting
- ✓ Application: Perfect for living rooms, pathways, balconies, facades etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.82
Unit CBM	0.00198

Listing Details

EAN Code	3800157616416
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	440

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES