



VT-7621PIR GU10 WALL FITTING WITH SENSOR, STAINLESS STEEL
BODY-1 WAY IP44

Dimensions
110x67x163mm

SKU:7502

2 YEARS
WARRANTY



Technical Information

Holder Type: GU10

Rated Load: Max 35W

Unit Color: STAINLESS STEEL

Body Type: Stainless Steel

IP Rating: IP44

Dimmable: No

Warranty (Years): 2

Operation Temperature: -25 to +50°C

Input Power: AC:220-240V,50Hz

Features

- ✓ Perfect replacement for traditional wall fittings
- ✓ Designed with Ingress protection of IP44
- ✓ Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only - Light not included)
- ✓ Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

Packaging

Unit Details

Gross Weight(GW) Kgs 0.62

Unit CBM 0.00146625

Master Box Packaging

Master Box Qty (Pcs Per Carton) 24

Qty Per Pallet 680

Listing Details

EAN Code 3800157617611

Commodity Code 9405109890

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES