



VT-730 WALL LAMP-MATT BLACK-UP E27

Dimensions
200x238mm

SKU:7046

2 YEARS
WARRANTY

Technical Information

Holder Type: E27

Rated Load: Max 40W

Unit Color: Black

Body Type: Aluminium + Glass

IP Rating: IP44

Dimmable: No

Warranty (Years): 2

Input Power: AC:220-240V,50Hz



Features

- ✓ Traditional Garden Lamps designed to fit the Modern day requirements
- ✓ Available in different designs, shapes and sizes
- ✓ Waterproof Lamps available in series of IP rating from IP44 to IP54
- ✓ Easy to Install and low Maintenance
- ✓ Suitable with E27 base lights(Fitting only - Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

Packaging

Unit Details

Gross Weight(GW) Kgs	0.9
Length(Box)mm	225
Width(Box)mm	215
Height(Box)mm	245
Unit CBM	0.01265

Listing Details

EAN Code	3800157610391
Commodity Code	9405109890



Master Box Packaging

Master Box Qty (Pcs Per Carton)	6
Qty Per Pallet	120

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES