

VT-7680 E27 WALL LAMP WITH STAINLESS STEEL & PC IP44

Dimensions
250x90x100mm

SKU:7514

2 YEARS
WARRANTY



Technical Information

Holder Type: E27

Dimmable: No

Rated Load: Max 14W

Warranty (Years): 2


Unit Color: White

Operation Temperature: -25 to +50°C

Body Type: Stainless Steel + PC

Input Power: AC:220-240V

IP Rating: IP44



Features

- ✓ Traditional Garden Lamps designed to fit the Modern day requirements
- ✓ Available in different designs, shapes and sizes
- ✓ Waterproof Lamps available in series of IP rating from IP44 to IP54
- ✓ Easy to Install and low Maintenance
- ✓ Suitable with E27 base lights(Fitting only - Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

Packaging

Unit Details

Gross Weight(GW) Kgs	0.5
Unit CBM	0.00286

Listing Details

EAN Code	3800157617734
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
---------------------------------	----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES