

VT-7670 E27 WALL LAMP WITH STAINLESS STEEL & PC IP44

Dimensions
250x90x100mm

SKU:7513

2 YEARS
WARRANTY



Technical Information

Holder Type: E27

Rated Load: Max 14W

Unit Color: White

Body Type: Stainless Steel + PC


IP Rating: IP44

Dimmable: No

Warranty (Years): 2

Operation Temperature: -25 to +50°C

Input Power: AC 220-240V, 50Hz



Features

- ✓ Traditional Garden Lamps designed to fit the Modern day requirements
- ✓ Available in different designs, shapes and sizes
- ✓ Waterproof Lamps available in series of IP rating from IP44 to IP54
- ✓ Easy to Install and low Maintenance
- ✓ Suitable with E27 base lights(Fitting only - Light not included)
- ✓ Application: Suitable for Garden, Floor, Ceiling etc

Packaging

Unit Details

Gross Weight(GW) Kgs	0.5
Unit CBM	0.00286

Listing Details

EAN Code	3800157617727
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	12
Qty Per Pallet	420

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES