



5W

VT-757 5W -WALL LAMP WITH BRIDGELUX CHIP COLORCODE:4000K ROUND-WHITE

Lumens 560	Beam Angle 360	Dimensions Ø140x65mm
----------------------	--------------------------	--------------------------------

Day White
SKU:7093


2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Instant Start: 0-100% in 11s	IP Rating: IP20
Watts: 5	Dimmable: No
Lumens: 560	Warranty (Years): 2
Shape: Round	PF: >0.45
Beam Angle: 360	CRI: >80
Unit Color: White	Operation Temperature: -25 to +50°C
Body Type: Aluminium	Input Power: AC:110-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes



Features

- ✓ 360 Degrees Rotatable Wall Light with adjustable beam angle from 10 to 360 degrees
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Excellent heat dissipation
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.08
Length(Box)mm	160
Width(Box)mm	150
Height(Box)mm	80
Unit CBM	0.0018

Listing Details

EAN Code	3800157616935
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	540

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES