



**6W**

VT-756 6W-WALL LAMP WITH BRIDGELUX CHIP COLORCODE:4000K  
 WHITE ROUND

Lumens <b>660</b>	Beam Angle <b>120</b>	Dimensions <b>140x115x100mm</b>
----------------------	--------------------------	------------------------------------

Day White  
 SKU:7091



## Technical Information

Instant Start: 0-100% in 11s	IP Rating: IP65
Watts: 6	Dimmable: No
Lumens: 660	Warranty (Years): 2
Shape: Round	PF: >0.45
Beam Angle: 120	CRI: >80
Unit Color: White	Operation Temperature: -25 to +50°C
Body Type: Aluminium	Input Power: AC:220-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes

## Features

- ✓ High Quality Bridgelux chips for reliable operation and lifetime
- ✓ Get range of up-down beams with Adjustable beam angle to feel range of aesthetics
- ✓ Constructed to high quality aluminum for efficient heat dissipation
- ✓ Cylindrical & Cubical fixtures in 3 colors to fit into range of architectural structures
- ✓ Elegant replacement for traditional up-down lighting
- ✓ Application: Perfect for living rooms, pathways, balconies, facades etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.81
Unit CBM	0.00198

### Listing Details

EAN Code	3800157616911
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	500

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES