



6W

VT-741 6W WALL LAMP WITH BRIDGELUX CHIP COLORCODE:4000K
 WHITE ROUND

Lumens 660	Beam Angle 360	Dimensions Ø135mm
----------------------	--------------------------	-----------------------------

Day White
 SKU:7525



Technical Information

Instant Start:	0-100% in lt1s	IP Rating:	IP65
Watts:	6	Dimmable:	No
Lumens:	660	Warranty (Years):	2
Shape:	Round	PF:	>0.55
Beam Angle:	360	CRI:	>80
Unit Color:	White	Operation Temperature:	-25 to +50°C
Body Type:	Die Cast Aluminium	Input Power:	AC:220-240V,50/60Hz
Long life:	20,000 Hours	Sensor Compatibility:	Yes
LED Chip Type:	SMD		



Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.55
Length(Box)mm	150
Width(Box)mm	150
Height(Box)mm	50
Unit CBM	0.001125

Listing Details

EAN Code	3800157620024
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	720

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES