



12W

VT-712 12W LED WALL LIGHT COLORCODE:3000K IP20 GREY BODY

Lumens 1100	Beam Angle 360	Dimensions 260x125x55mm
-----------------------	--------------------------	-----------------------------------

Warm White
SKU:8206




Technical Information

Instant Start: 0-100% in 1/1s	Dimmable: No
Watts: 12	Warranty (Years): 2
Lumens: 1100	PF: >0.5
Beam Angle: 360	CRI: >80
Unit Color: Grey	Operation Temperature: -20 to +45°C
Body Type: Aluminium + Acrylic	Input Power: AC:100-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes
IP Rating: IP20	

Features

- ✓ Perfect choice of Interior lighting for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	1.13
Length(Box)mm	280
Width(Box)mm	145
Height(Box)mm	75
Unit CBM	0.003045

Master Box Packaging

Inner Box Qty	20
Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	320

Listing Details

EAN Code	3800157623230
Commodity Code	9405403990

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES